



EVO-STIK Sanitary Silicone Sealant

ACETOXY SILICONE SEALANT

Date: 12 January 2016

Fact Sheet No.: TDS00210

YOUR SMART ADVANTAGES

- High quality moisture curing, acetoxy silicone sealant
- Contains a fungicide
- Ideal for sealing around sanitary fittings in kitchens and bathrooms

USES

EVO-STIK Trade Only Sanitary Sealant is a high quality moisture curing, acetoxy silicone sealant. It contains a fungicide and is ideal for sealing around sanitary fittings in kitchens and bathrooms. EVO-STIK Trade Only Sanitary Sealant is ideal for jointing between tiles and baths, basins, shower trays, kitchen worktops and stainless sink tops. It provides excellent adhesion to non-porous surfaces such as glass, stainless steel and ceramics. EVO-STIK Trade Only Sanitary Sealant is waterproof immediately after application and fast setting, usually less than 24 hours.

PRODUCT CHARACTERISTICS

| | | | |
|------------------|---|-------|----------|
| Colour | White & Translucent (Clear) | | |
| Form | Thixotropic paste | | |
| Specific Gravity | 0.94 approx. | | |
| Composition | Moisture curing, acetoxy type, silicone | | |
| Product Codes | 30812745 | White | C20 x 12 |
| | 30812744 | Clear | C20 x 12 |
| | 30814526 | White | C20 x 6 |
| | 30814527 | Clear | C20 x 6 |

Storage/Shelf Life

Store for up to 24 months from date of manufacture when stored in original, unopened packaging under cool, dry conditions within the temperature range of +5°C to +25°C and out of direct sunlight. Protect from frost.

Odour

'Vinegar' odour of acetic acid whilst curing

TYPICAL PERFORMANCE DATA (Approx.)

Application Temperature

+5°C to +40°C

Service Temperature

-30°C to +80°C

Coverage

10 linear metres of 6mm diameter bead per C20 cartridge

Drying Times

Skin Formation: 30 to 40 minutes dependent on bead width, temperature and humidity.

Through Dry: Approx. 2 - 3 mm per 24 hours dependent on bead width, temperature and humidity.

Always tool sealant within 20 minutes of application

DIRECTIONS FOR USE

IMPORTANT: Before using EVO-STIK Trade Only Sanitary Silicone Sealant refer to the relevant Health & Safety Data Sheet, available at www.bostik.co.uk.

PREPARATION

1. Work in warm but well ventilated conditions.
2. Joint surfaces must be clean, dry, sound and free from dust, loose material and other contaminants that may impair adhesion.



FM 01696
BS EN ISO 9001:2008

Bostik Limited, Common Road, Stafford, ST16 3EH, UK. Tel: +44 (0) 1785 272625 www.bostik.co.uk

Bostik, Evo-Stik & Sealocrete are registered trademarks of Bostik Ltd.

3. If desired place masking tape along the joint edges before application. This can make it easier to make a neat, tooled finish. Use a spatula with a round end to tool the sealant and check that this tool just fits into the gap between the masking tape so that it catches the excess sealant.
4. Do a test run without applying any sealant to 'get a feel' for the difficult areas to seal in corners, behind taps and raised joints.

APPLICATION

5. Unscrew the nozzle, and using a sharp knife, carefully cut off the dome of the cartridge, taking care not to damage the thread. Screw the nozzle onto the cartridge.
6. Cut off the tapered end of the nozzle at a 45° angle, to a width matching the gap to be sealed.
7. Fit the cartridge into the cartridge gun by pressing the release plate and pulling out the plunger. Insert cartridge and repeatedly squeeze the trigger until the sealant appears.
8. Place the nozzle at the start of the gap, and gently squeeze the trigger. Push forward slowly, ensuring that contact is made by the sealant with both sides of the gap. At the end of the run, release the trigger and press the plunger release plate of the gun.
9. Smooth the sealant with a wet, round ended tool (do not use a wetted finger), remove any excess with a cloth moistened with white spirit and then remove the masking tape (if used) from either side of the bead.
10. After use, ensure to wipe away any excess adhesive from the nozzle. Replace the cap.
11. The sealant skins over rapidly (approx. 30 minutes) and is fully cured in 24 hours depending on bead width, temperature and humidity.

CLEANING

Uncured Sealant:

12. Excess uncured sealant should be removed carefully using a soft scraper. The remainder can be removed using a cloth just moistened with white spirit. Repeat using another clean cloth moistened with white spirit.

Cured Sealant:

13. There is no adequate solvent; carefully cut away excess with a very sharp knife. Do not use solvent to remove product from skin – use soap and water.
14. For the sealant to continue to work effectively, ensure that it is cleaned regularly and not submersed under water.
15. In bathrooms and kitchens, occasionally wipe the sealant with diluted bleach (5 parts water : 1 part bleach) to aid resistance to mould.

PRECAUTIONS IN USE

EVO-STIK Trade Only Sanitary Silicone Sealant cannot be applied to surfaces which have frost or ice on them. Do not use on zinc, lead or cement based surfaces. Will not resist abrasion in floor joints. Do not use in swimming pools. Do not use for aquarium applications. Prevent entry of uncured sealant into drains or watercourses. Do not use on or near bitumen. Not suitable for bedding double glazed/insulating glass units into frames. Will not accept paint and must not be painted. Do not submerge under water.

For any application not covered please contact Technical Services on +44 (0)1785 272625 or visit www.bostik.co.uk for advice.

Recommendations and suggestions are for guidance only, since conditions of use are completely beyond our control.

For health and safety instruction, first aid measures and spillage and disposal instructions, see separate Health and Safety Data Sheet for EVO-STIK Trade Only Sanitary Silicone Sealant, available at www.bostik.co.uk.



FM 01696
BS EN ISO 9001:2008

Bostik Limited, Common Road, Stafford, ST16 3EH, UK. Tel: +44 (0) 1785 272625 www.bostik.co.uk

Bostik, Evo-Stik & Sealocrete are registered trademarks of Bostik Ltd.

**CONSTRUCTION PRODUCT REGULATION
DECLARATION OF PERFORMANCE**

No.:TDS00210

Product Description: **EVO-STIK Trade Only Sanitary Silicone Sealant (White & Clear)**
 Product Code: **5010591999947, 5010591999930**
 Intended Use: **Sanitary Sealant**
 Manufacturer: **Bostik Ltd**
 Contact Address: **Common Road
Stafford
ST16 3EH**
 System of Assessment: **System 3**
 Harmonised Standard: **BS EN 15651-3:2012**
 Notified Body: **0074**
 Declared Performance:

| Essential Characteristics | Performance | Harmonised technical specification |
|---------------------------|-------------|------------------------------------|
| Reaction to Fire | F | BS EN 15651-3:2012 |
| Release of Chemicals | None | See Safety Data Sheet |

Water Tightness & Air Tightness as determined by:

| | | |
|--|-------------|---------------------------|
| Resistance to Flow | NPD | BS EN 15651-3:2012 |
| Loss of Volume | NPD | |
| Tensile properties after immersion in water at 23°C* | ≥25% | |
| Microbiological Growth | NPD | |
| Durability | NPD | |

***Conditioning method A, tested on Aluminium Substrate, no primer**

The performance of the EVO-STIK Trade Only Sanitary Silicone Sealant 5010591999947 and 5010591999930 is in conformity with the declared performance shown in the table above.

This declaration of performance is issued under the sole responsibility of Bostik Ltd.

Signed for and on behalf of Bostik Ltd by:

Name: Alison Jamieson

Function: S.H.E.Q. Manager

Signature: 

Date: June 2014



FM 01696
BS EN ISO 9001:2008

Bostik Limited, Common Road, Stafford, ST16 3EH, UK. Tel: +44 (0) 1785 272625 www.bostik.co.uk
 Bostik, Evo-Stik & Sealocrete are registered trademarks of Bostik Ltd.

This disclaimer is issued by Bostik Limited ("the Company") and applies to the use of any products supplied by the Company ("the Products") displayed on this Technical Data Sheet ("TDS"). Please read this disclaimer carefully before using any of the Products. Using this TDS and/or the Product constitutes your acceptance of this disclaimer. Its contents shall prevail over any directions of use and any disclaimer and/or exclusion or limitation of liability of the Company which may appear on the packaging of the Products.

This disclaimer sets out the entire financial liability of the Company (including any liability for the acts or omissions of its employees, agents and sub-contractors) to any user of the Products ("Product User") in respect of any use made or resale by the Product User, of any of the Products in this TDS.

This disclaimer does not affect the Company's liability for death or personal injury arising from the Company's negligence in respect of the Products, nor its liability for fraud, or fraudulent misrepresentation, nor any other liability which cannot be excluded or limited under applicable law.

The Company's total liability however arising and whether caused by tort (including negligence and breach of statutory duty), breach of contract or otherwise, arising in connection with the use made or resale by the Product User of any of the Products in this TDS shall be limited to the price paid for the Product by the Product User.

The Company shall not be liable to the Product User for any pure economic loss, loss of profit, loss of business, depletion of goodwill or otherwise, in each case whether direct, indirect or consequential, or any claims (including in respect of personal injury insofar as not caused by the Company's negligence) for consequential compensation whatsoever (howsoever caused) which arise out of or in connection with the use made or resale by the Product User of any of the Products in this TDS.

The Company shall not be liable to the Product User in relation to any loss for any use which is inappropriate or use which is otherwise than in accordance with the relevant instructions for use of the Products in this TDS or on the Product. Product Users are advised to confirm the suitability of the Products by their own tests.

This TDS covers just one of a large range of products supplied by the Company.

Full information on these products and advice on application is freely available from our fully trained staff throughout the country. In addition, specialist technical advice is available from our Technical Services Department. This TDS supersedes all previous TDSs relating to the Products, and users of it must ensure that it is the current issue. Destroy all previous TDS, and if in any doubt, contact the Company, quoting the code number in the top right hand corner on the front of this document.

| | | | |
|---|--------------------|-------------------|--|
| Sales | Tel: 0844 371 1192 | Fax: 01785 241818 | customer.service@bostik.com |
| Technical Advice | Tel: 0844 371 1197 | Fax: 01785 272867 | technical.service@bostik.com |
| Technical Data & COSHH (MSDS) Data Sheets | Tel: 01785 272625 | Fax: 01785 212962 | stafford.gatehouse@bostik.com |



FM 01696
BS EN ISO 9001:2008

Bostik Limited, Common Road, Stafford, ST16 3EH, UK. Tel: +44 (0) 1785 272625 www.bostik.co.uk
Bostik, Evo-Stik & Sealocrete are registered trademarks of Bostik Ltd.